INTRINSICALLY SAFE

EK-AEP SERIES

Compact Balances







EK-AEP: Areas Certified for Safe Use

	Flammable gases/vapors present continuously	Flammable gases/vapors present intermittently	Flammable gases/vapors present only accidentally
IECEX ATEX FM/FMc (NEC505)	Zone 0	Zone 1	Zone 2
FM/FMc (NEC500)	Divis	Division 1	

The balance can be used in locations where ignitable concentrations of flammable gases, vapors or liquids are present for long periods. (i.e. Zone 0 or Division 1).



IECEx: Ex ia op is IIB T3 Ga
ATEX: II 1G Ex ia op is IIB T3 Ga
FM/FMc (NEC505): Class I, Zone 0, AEx/Ex ia op is IIB T3
FM/FMc (NEC500): IS / I / 1 / C,D / T3C

Tamb -25 to +40°C



Avoid expense of special wiring for securing power from an area with a safety barrier.

ONLY FOR USE WITH:

Duracell AA Alkaline MN1500 LR6 Energizer AA E91 Alkaline LR6 AM3 Panasonic AA Alkaline LR6 (XJ) 1.5V batteries.

Safe and Connected Weighing Solution



FEATURES:

- Hygienic and chemically resistant stainless steel (SUS304) weighing pans
- · Easy-to-read backlit LCD display
- Multiple weighing units: g, oz, lb, ozt, ct, mom, dwt, gr, N, in addition to pcs (counting mode),
 % (percent mode) and SG (specific gravity)
- GMP/GLP compliant output to meet documentation requirements
- Auto power OFF function to save battery- power)
- Comparator function for fast and accurate filling, packing, sorting, etc
- Adjustable response characteristics to offset drafts and vibrations
- Security ring for wire-locking the balance to prevent theft

AD-1611




AD-1611 optical communication adapter for data output (sold separately). The AD-1611 connect the EK-AEP to an external device such as a printer or PC through RS-232C or USB.

Accessory



Optical fiber cable to connect EK-AEP and AD-1611 available in 10 m, 30 m, and 60 m.

Setup Image:



Specifications

EK-AEP Series		EK-300AEP	EK-3000AEP	EK-12KAEP	
Weighing capacity		300 g	3000 g	12 kg	
Minimum weighing value		0.01 g	0.1 g	1 g	
Repeatability (Standard Deviation)		0.01 g	0.1 g	1 g	
Linearity		±0.02 g	±0.2 g	±1 g	
Sensitivity drift		±20 ppm/°C (10 to 30°C/50 to 86°F)			
Counting mode	Min. unit mass*i	0.01 g	0.1 g	1 g	
	No. of samples	5, 10, 25, 50 or 100 pieces			
Percent mode	Min. % display	0.1%			
	Min. 100% reference mass	1 g	10 g	100 g	
Display		7 segment LCD (character height: 16 mm) with backlight			
Display refresh rate		Approx. 10 times/second			
Operating temperature and humidity		0 to 40°C/32 to 104°F, 85% RH or less (no condensation)			
Battery life		Approx. 250 hours (with four AA alkaline batteries*ii, backlight off)			
Weighing pan size		Ø110 mm	133 × 170 mm		
Dimensions		190 (W) × 218 (D) × 54 (H) mm	190 (W) × 218 (D) × 53 (H) mm		
Net weight		Approx. 1.2 kg	Approx. 1.5 kg		
Calibration weight*i		300 g	3000 g	10 kg	

^{*}i Factory setting

AD-1611

Power supply	AC adapter or USB	
Operating temperature and humidity	-10 to 40°C/32 to 104°F, 85% RH or less (no condensation)	
Baud rate	According to the value set on the balance	
Receiving connector	F05 (IEC 60874-17, F05 type)	
Sending connector	RS-232C (D-Sub 9 pin) or USB (type B)	
Optical transmission distance	Max. 60 m (no extension available)	
Dimensions	160 (W) × 58 (D) × 38 (H) mm	
Net weight (main unit only)	Approx. 380 g	
Standard accessories	AC adapter, USB cable	

Accessories

AX-KS5456-010	Optical fiber cable (10 m)	
AX-KS5456-030	Optical fiber cable (30 m)	AX-KS5456-030
AX-KS5456-060	Optical fiber cable (60 m)	

Standard functions

















^{*}ii To be used only with four DURACELL AA alkaline MN1500 LR6, ENERGIZER AA E91 alkaline LR6 AM3, or Panasonic AA alkaline LR6 (XJ) 1.5V batteries.