ezEX-RJ45[®] Termination System

Connectors





A CONTRACTOR


EXO[™] Crimp Frame + EZ-RJ45[®] Die terminates EZ-RJ45[®] Connectors

We Make Connections EZ!™

In today's networks, twisted pair cables are demanding more speed and bandwidth. To help meet these requirements, Cat5e/6/6A cables have increased in size. Both the outer diameter of the cable and the insulation diameter of the conductors are larger and vary by manufacturer, making cable and connector compatibility a challenge. The new patented **ezEX-RJ45®** Termination System is the solution — providing greater cable to connector compatibility to meet higher performance demands. The ezEX-RJ45[®] connectors feature a unique integrated Hi-Lo stagger load bar and allows 'big' conductors to pass through the front end of the connector making it easy to verify the wiring sequence before terminating.

ezEX-RJ45[®] Connectors

- Simple one piece/pass through design, no bars or liners
- Rated up to 10 Gigabit for superior performance
- Works with solid or stranded conductors from 24-22 AWG
- FCC, RoHS 2 & UL compliant
- Made in USA



• .043" - .048" (1.09 - 1.22mm)

Ordering Information:

-							
Connectors	Insulation Diameter (Conductor) Range	Max Outer Diameter	P/N	Package Quantity			
ezEX™44	.039"044" (1.0-1.12mm)	.290" (7.36mm)	202044J	100 pcs/Jar			
ezEX™48	.043" – .048" (1.09 – 1.22mm)	.290" (7.36mm)	202048J	100 pcs/Jar			

EXO[™] Crimp Frame and EXO Die[™]

- Single cycle crimp and flush trim
- EXO Die[™] is easily interchangeable
- Reversible EXO Die[™] for ambidextrous operation
- Connectors lock into tool for correct positioning during crimp
- Push button lock for easy storage
- Ergonomic comfort grip TPR handles

Ordering Information

Product	P/N	Compatible Connectors
EX0 [™] Crimp Frame with EXO-EX Die	100061C	ezEX-RJ45® Connectors
EXO-EX Die only	100071C	ezEX-RJ45 [®] Connectors
EXO [™] Crimp Frame with EZ-RJ45 [®] Die	100062C	EZ-RJ45 [®] Connectors
EZ-RJ45 [®] Die only	100072C	EZ-RJ45 [®] Connectors









User Guide

Prep and Crimping ezEX-RJ45[®] Connectors

- 1. Remove cable jacket leaving 1" to 1 1/2" of conductors. If there is a pair separator, remove it by cutting flush at the end of the cable.
- 2. Untwist all 4 pairs and comb out all twists so conductors can lay side by side with no gaps. Configure your pairing to the T568 A or B. See chart below.
- 3. Cut all 8 ends even, insert into rear of connector, and push through and out the front end.
- Insert prepped connector into the EXO Die[™] and







4

listen for the 'click'. It is now 'locked' in and ready to be crimped. Squeeze handles together slowly until they come to a stop. Release, unlock the connector and remove from the EXO Die.

Ready to use




				Patiente Baue				
Wire	1	2	3	4	5	6	7	8
T568A	W/G	G	W/0	BL	W/BL	0	W/BR	BR
T568B	W/0	0	W/G	BL	W/BL	G	W/BR	BR

We Make Connections EZ!™

Using the EX0[™] Crimp Frame

- 5. **To Unlock** squeeze handles together and hold, pushing the lock button on the back side all the way through to the front side and release the handles. The tool will now open.
- 6. To Lock squeeze handles together and hold, pushing the lock button on the front side all the way through to the back side and release handles. The tool is now in closed/locked position.
- Removing EXO Die[™] Using both thumbs (see 7.1), simultaneously push in the locking tabs (see 7.2), and while holding in place, push the EXO Die toward and out the backside of the EXO Crimp Frame. Keep die set parallel to the frame to prevent jamming (see 9).
- Replacing EXO Die[™] Same as removing the die set BUT in reverse.
- 9. Keep die set parallel to frame to prevent jamming for both removing or replacing.











03.17 Platinum Tools, All rights reserved