

Large Volume Stirrers



5 Commonwealth Ave Woburn, MA 01801 Phone 781-665-1400 Toll Free 1-800-517-8431



/isit us at www.TestEquipmentDepot.com



Powerful Motor and Magnet Mixes Samples Up To 200 L

OHAUS offers four models for stirring capacities between 25 to 200 L, allowing you to choose the right model for your application. The broad top plate surface allows processing of oversized vessels such as carboys for your large volume stirring. The powerful magnetic drive is also capable of mixing highly viscous materials.

Unique Features Include:

- High Volume Stirrers (STLC1DG and STLC2DG) with a 100 or 200 L capacity are made with a stainless steel base offering durability and stability, and feature a 54 x 63 cm stainless steel top plate.
- High Volume Stirrers (STHVAL and STHVDG) have a large 32 x 28 cm top plate that is chemical-resistant with a white reflective surface that is easy to clean. Digital and non-digital models allow you to choose the right model for your application.
- Speed ramping feature slowly increases the motor speed for improved safety and enhanced coupling. Avoids splashing, improves spin bar control and provides excellent low-end speed control.

Large Volume Stirrers

Model	STHVAL	STHVDG	STLC1DG	STLC2DG
Control	Analog	Digital		
Speed Range	60 rpm to 1400 rpm		100 rpm to 1800 rpm	100 rpm to 1650 rpm
Timer	N/A	1 second to 160 hours		
Capacity	25 L		100 L	200 L
Plate Construction	Glass Filled Nylon		Stainless Steel	
Dimensions (H x L x W)	4 x 17 x 11 in. / 10.2 x 43.2 x 27.9 cm		5.25 x 28.5 x 26.75 in. / 13.3 x 72.4 x 68 cm	
Plate Dimensions (L x W)	12.5 x 11 in. / 31.8 x 27.9 cm		21.25 x 25 in. / 54 x 63.5 cm	
Net Weight	13.6 lb / 6.2 kg		63.5 lb / 28.8 kg	
Power	120 V, 50/60 Hz		120 V, 50/60 Hz	
Power Consumption	75 W	90 W		
Working Environment	41 °F – 104 °F, 80% RH*, non-condensing / 5 °C – 40 °C, 80% RH*, non-condensing			

^{*}RH = Relative Humidity

Other Standard Features & Equipment

High Volume Stirrers feature a cast aluminum housing and glass filled nylon top plate. Large Capacity Stirrers feature a stainless steel top plate and aluminium housing. Models include either a 70 mm egg shaped stir bar (STHVAL, STHVDG, STLC1DG) or 102 mm stir bar with pivot ring (STLC2DG). Speed ramping feature slowly increases motor speed for enhanced coupling and improved stirring. Microprocessor-controlled for precise speed regulation. Timer counts up or when programmed to a set time, will turn off stirring and sound alarm when timer reaches zero.

Compliance


- Product Safety: CAN/CSA C22.2 No. 61010-1, CAN/CSA C22.2 No. 61010-2-051, UL 61010-1
- Electromagnetic Compatibility: ICES-003 Class A, FCC Part 15 Class A
- Compliance Marks: UL (for STHVAL and STHVDG) and TUV (for STLC1DG and STLC2DG)

Accessories

Dimensional Drawings


STHVAL


STLC1DG



STHVDG

279 mm





432 mm

97 mm

3.8 in.

30776575_G 20200609 © Copyright OHAUS Corporation

OHAUS CORPORATION



^{*}Included with STHVAL, STHVDG, STLC1DG

^{**}Included with STLC2DG