



Mastercool[®]
"World Class Quality"

90066-EX-HOSE/90068-EX-HOSE EXHAUSE HOSE ASSEMBLY INSTRUCTION MANUAL



- Utilize with all Mastercool "Black Series" vacuum pumps
- Vent exhaust fumes in tight quarters
- Highly recommended when servicing systems running on A2L and A3 flammable refrigerants

INSTRUCTIONS:

1. Disassemble existing exhaust from vacuum pump
2. Connect new assembly to the same exhaust location
3. Exhaust the end of the hose assembly to a safe and well ventilated location

PARTS:

90066-EX-HOSE

- | | |
|-------------|---|
| 90066-PH | Clear Plastic Hose by Meter |
| 90066-CLAMP | Stainless Steel Clamp |
| 90066-EX | Vacuum Pump Exhaust for 1.5, 3 & 6 CFM models |

90068-EX-HOSE

- | | |
|-------------|---|
| 90066-PH | Clear Plastic Hose by Meter |
| 90066-CLAMP | Stainless Steel Clamp |
| 90068-EX | Vacuum Pump Exhaust for 8 & 12 CFM models |

⚠ **WARNING:** Cancer and Reproductive Harm – www.P65Warnings.ca.gov

For parts or service please contact the service department