

# WaveSource Pro Operations Guide Fiber Optic Light Sources



**Optical Wavelength Laboratories**

---

Operations Guide

Date: November 20, 2017

WaveSource Pro Fiber Optic Light  
Sources

Version 1.0



5 Commonwealth Ave  
Woburn, MA 01801  
Phone 781-665-1400  
Toll Free 1-800-517-8431

 Visit us at [www.TestEquipmentDepot.com](http://www.TestEquipmentDepot.com)

<b>CONTENTS</b>	<b>PAGE</b>
1.0 GENERAL	2
2.0 FUNCTIONAL DESCRIPTIONS	3
2.0.1 WAVESOURCE CONNECTIONS	3
2.0.2 WAVESOURCE INDICATOR LEDs	3
2.0.3 WAVESOURCE BUTTONS	3
3.0 APPLICATIONS	4
3.1 PRECAUTIONS	4
3.1.1 Safety	4
3.1.2 Operational	4
3.1.3 Connector	4
3.2 REQUIRED ACCESSORIES	4
3.2.1 Cleaning Supplies	4
3.2.2 Patch Cords	4
3.2.3 Optical Fiber Adapters	4
3.3 TYPICAL APPLICATIONS	4
4.0 MAINTENANCE / CALIBRATION	5
5.0 WARRANTY	5
6.0 SPECIFICATIONS	6
7.0 WAVESOURCE CONFIGURATIONS	6

---

## **FIGURES**

Figure 1 - WaveSource Fiber Optic Light Source	3
--	---

## 1.0 GENERAL

Thank you for your purchase of an Optical Wavelength Labs (OWL) WaveSource Pro fiber optic light source.

WaveSource Pro series fiber optic light sources offer the fiber optic professional a wide range of options for their testing needs. Different combinations of multimode, singlemode, and VFL ports are available:

WPMS -- quad-wave (MM: 850/1300nm; SM: 1310/1550nm)

WPMX -- Multimode 850/1300nm

WPMV -- Multimode 850/1300nm; VFL

WPSX -- Singlemode 1310/1550nm

WPSV -- Singlemode 1310/1550nm; VFL

VFLs can be used in both multimode and singlemode fibers.

All versions of the WaveSource Pro have two transmission modes: Continuous Wave (CW) for accurate temperature-stabilized fiber optic tests; and modulated mode.

In addition, WaveSource Pro light sources speed up the testing process through an advanced feature called AUTO mode when used with a Fiber OWL 7 optical power meter.

While in AUTO mode, both the WaveSource Pro and Fiber OWL 7 automatically switch between two wavelengths, so that both wavelengths can be measured simultaneously. This eliminates much of the guesswork during testing, and saves valuable time.

WaveSource Pro light sources come configured with SC connector ports. ST or FC connector ports are available upon request.

Typical uses include telecommunications networks, data networks, cable television, and industrial equipment control.

## 2.0 FUNCTIONAL DESCRIPTIONS



Figure 1 - WaveSource Pro  
Fiber Optic Light Source

### 2.0.1 CONNECTIONS

1. Light source connector port (left)  
SC connector (ST or FC available upon request)
2. Battery charging port (USB)
3. Light source connector port (right)  
SC connector (ST or FC available upon request)

### 2.0.2 INDICATOR LEDs

4. Port selection LED (left)  
Lit when the left-hand port is active
5. Power/Battery charger LED  
Lit when unit is powered on  
*Battery/charging status*  
**GREEN** battery fully charged  
**ORANGE** battery charging  
**RED** problem with battery and/or charger
6. Port selection LED (right)  
Lit when the right-hand port is active
7. Wavelength display LED  
Displays current output wavelength when lit  
Powers off after 3 seconds; press power button to show wavelength

### 2.0.3 BUTTONS

8. CW / MOD button  
Press: toggle source between CW (continuous wave) and MOD (modulated) mode.
9. Power button  
Hold: power on and off  
Press: display wavelength
10.  $\lambda$  / AUTO button  
Press: toggle between wavelengths in the selected port  
Hold: set AUTO mode; source alternates wavelengths within the active port for automatic dual-wavelength testing
11. PORT button  
Press: toggle between light source ports

## 3.0 APPLICATIONS

### 3.1 PRECAUTIONS

3.1.1 Safety - Exercise caution when working with optical equipment. Most transmission equipment and light sources use light that is invisible to the human eye. High energy light is potentially dangerous, and can cause serious, irreparable damage to the eye. Thus, it is recommended to **NEVER** look into the connector port of any light source or the end of a fiber.

3.1.2 Operational - In order to ensure accurate and reliable readings, it is vitally important to clean ferrules containing optical fibers and optical connector ports. If dirt, dust, and oil is allowed to build up inside connector ports, this may scratch the emitting surface of the light source, producing erroneous results. Replace dust caps after each use.

3.1.3 Connector - do NOT insert APC (Angled Physical Contact) connectors into the optical ports on the WaveSource Pro as this may damage the light source inside the ports.

### 3.2 REQUIRED ACCESSORIES

3.2.1 Cleaning Supplies - It is recommended to clean fiber ferrules before each insertion with 99% or better isopropyl alcohol and a lint free cloth. A can of compressed air should be available to dry off the connector after wiping, and to blow out dust from bulkheads.

3.2.2 Patch Cords - Patch cords may be needed to connect the WaveSource Pro to the system under test for optical loss measurement. The connector styles on the patch cord must match the type on the WaveSource Pro and the type of the system under test.

3.2.3 Optical Fiber Adapters - Optical fiber adapters are used to connect two connectorized fibers together, and may be necessary to adapt the test cords to the system under test.

### 3.3 TYPICAL APPLICATIONS

WaveSource Pro light sources can be used as diagnostic and measurement tools of optical transmission systems and fiber optic links. These applications can be found in several industries, including premise, LAN, CATV, and Telco.

WaveSource Pro fiber optic light sources are designed to emit a temperature-stabilized source of light to be used for optical loss measurement. The WaveSource Pro serves as an optical reference, which is otherwise known as the "zero" point when a power meter is "zeroed". Optical loss measurements are useful for measuring the attenuation, or loss, of a fiber link. The loss value can then be compared to a pre-calculated link budget, which is used to determine if the fiber link will operate within the parameters of the transmission equipment.

The formula for calculating loss in a fiber link is:

$$L = P_a - P_r$$

where **L** is the amount of optical loss in dB, **P<sub>a</sub>** is the absolute power in dbm, and **P<sub>r</sub>** is the reference power in dBm.

Optical loss measurements can also be used for fiber optic link certification. Link certification is a process where optical loss measurements are compared to a link budget calculated using fiber optic cabling standards.

## **4.0 MAINTENANCE / CALIBRATION**

- 4.0.1 Repair of this unit by unauthorized personnel is prohibited, and will void any warranty associated with the unit.
- 4.0.2 The re-chargeable battery is fully enclosed inside the unit. A battery charger is provided for re-charging.
- 4.0.3 For accurate readings, the optical connectors on the WaveSource Pro and the connectors on the patch cords should be cleaned prior to attaching them to each other. Minimize dust and dirt buildup by replacing the dust caps after each use.
- 4.0.4 It is recommended to have Optical Wavelength Laboratories calibrate the WaveSource Pro once per year.

## **5.0 WARRANTY**

- 5.0.1 Optical Wavelength Labs products have a **two-year** factory warranty, which covers manufacturer defect and workmanship only, valid from the date of shipment to the original customer.
- 5.0.2 Products found to be defective within the warranty will be either repaired or replaced, at the option of Optical Wavelength Labs.
- 5.0.3 This warranty does not apply to units that have been repaired or altered by anyone other than Optical Wavelength Labs, or have been subjected to misuse, negligence, or accident.
- 5.0.4 In no way will Optical Wavelength Labs liabilities exceed the original purchase price of the unit.
- 5.0.5 To return equipment under warranty, please contact Optical Wavelength Labs for a RMA number. To ensure quick turnaround, please include a short description of the problem and a phone number where you can be reached during normal business hours.

## 6.0 SPECIFICATIONS

Optical Specifications	Multimode	Singlemode	VFL
Source Type	LED	Laser	Laser
Calibrated Wavelengths	850, 1300nm	1310, 1550nm	650nm
Output Power (CW)	-20 dBm (into MM fiber)	-10 dBm (into SM fiber)	-0 dBm
Accuracy	±0.10 dB @ 25°C	±0.10 dB @ 25°C	
Light Source Drift (1 hour)	±0.05 dB (850nm) ±0.05 dB (1300nm)	±0.05 dB (1310nm) ±0.04 dB (1550nm)	
Spectral Width (FWHM)	50nm (850nm) 180nm (1300nm)	2nm (1310nm) 3nm (1550nm)	
Modulation Frequencies	300 Hz = 850nm 600 Hz = 1300nm	1 kHz = 1310nm 2 kHz = 1550nm	

### General Specifications

Battery Life	up to 150 hours normal usage (lithium polymer)
Optical Connector	SC (ST or FC available upon request)
Operating Temperature	-20°C to +70°C
Storage Temperature	-40°C to +85°C
Dimensions	2.87 x 4.42 x 1.25 in
Weight (with battery)	10 ounces

## 7.0 CONFIGURATIONS

Part Number	Multimode		Single-mode		Part Number Legend WP(source1)(source2)
	Wavelengths	Connectors	Wavelengths	Connectors	
WPMS	850, 1300	SC	1310, 1550	SC	M = 850/1300 MM
WPMX	850, 1300	SC	N/A	N/A	S = 1310/1550 SM
WPMV	850, 1300	SC	<b>650nm VFL*</b>	SC	V = 650nm VFL
WPSX	N/A	N/A	1310, 1550	SC	X = no additional source installed
WPSV	<b>650nm VFL*</b>	SC	1310, 1550	SC	

\* VFL stands for Visual Fault Locator. VFLs will work in both multimode or single-mode fibers.